




Portable Steam Generators - Accessories

Barrel Steam Wand



Modeled after a century old Bordeaux design, the SWASH™ Barrel Steam Wand is elegant in simplicity and functionality. Steam is uniformly and safely distributed in the barrel for effective tartrate removal and barrel sanitization. Recent evidence shows that with the technique we recommend, residual wine is removed from the pores of the wood with little or no erosion of the toast.

General Purpose Steam Gun



The SWASH™ steam gun with its 42" lance, is long enough to safely allow steam cleaning of hard surfaces and is very effective on floor drains.

It is insulated to protect the individual using it.

Steam Hose with Fittings



The SWASH™ hose/fitting package is specifically designed to connect the SWASH™ steam generator to the various accessories you have purchased or directly to your equipment. The hose is steam rated to 100 psig and temperatures of up to 338°F/170°C.

It is designed for food contact, making it safe for all typical steam applications. The SWASH system includes custom sanitary connectors that serve as flow regulators, and are the only steam "Boss Clamp" compatible sanitary fittings available, further insuring safety.

Steam In Place (SIP) Assembly



The Steam In Place (SIP) assembly allows you to turn a length of stainless steel sanitary pipe into effectively an autoclave. By applying low pressure steam at not greater than 20psi, an internal pipe temperature can be maintained in excess of 250°F (121°C) to achieve medical grade sterilization.

Automatic Steam Controller



The SWASH™ steam controller allows for automatic on/off control to sterilize a bottling line including a filter block assembly from one steam generator without personnel present to start the process.

A dual controller is also available to separately sterilize the bottling line and filter block assembly if desired.

BarrelScope™ Inspection Device



The SWASH™ BarrelScope™ Inspection Device is a miniature lighted periscope with very high precision lenses that permits quick and convenient inspection about 85% of the interior of a barrel. The powerful 200 lumen LED light illuminates a field of view slightly

larger than the viewing area. The magnification through the focused viewing lenses permits inspection of the surface of the barrel in great detail. For new barrels, it affords a simple means to inspect incoming purchases. For used barrels, it allows visual inspection of the condition of the interior surface of the barrel without pulling the heads.

ABOUT SWASH SANITIZING EQUIPMENT

SWASH Sanitizing Equipment is an operating division of ARS Enterprises. ARS was established in 1971 to provide sterilizing and washing equipment and field maintenance and repair services to food and beverage firms, hospitals, laboratories and pharmaceutical or medical device manufacturers. Our equipment and service have earned us an outstanding reputation among our customers who have come to rely on ARS.

Our philosophy is to provide dependable equipment incorporating high quality components. The ARS team is dedicated to the highest standards of workmanship. Our pride rests on your satisfaction with the products and service we provide. We believe that with ARS you can achieve many years of reliable performance and an overall low cost of ownership.